

@echo off

rem -----

rem

rem This script provides a template for customizing and launching the
rem JT2Go 13.2 installer. Controlling the installer in this manner will:

rem

rem * allow for preselection of features to be installed

rem * prefill required fields (e.g. licensing options)

rem * ease deployment to a large number of users.

rem

rem To use this script, simply uncomment and fill in the proper options
rem below, and choose the proper options for the install, or feel free
rem to otherwise modify it to fit your situation.

rem

rem For some Windows Installer options, there are more possible values than

rem are listed here. For the complete Windows Installer command line reference, see

rem http://msdn.microsoft.com/library/default.asp?url=/library/en-us/msi/setup/command_line_options.asp

rem

rem -----

setlocal

set EXEFILE=JT2GoSetup.exe

set OPTIONS=

rem -----

rem Silent mode. OPT1 is for the .exe wrapper, OPT2 is standard Windows
rem Installer silent mode option. Both must be set.

rem -----

rem set SILENTOPT1=/S &set SILENTOPT2=/qb

rem -----

rem Installer logging

rem -----

rem set OPTIONS=%OPTIONS% -l*v C:\temp\JT2GoIns.log

rem -----

rem set the language in which to run the installer

rem -----

set ILANG=/L1033 &rem English

rem set ILANG=/L1036 &rem French (Standard)

rem set ILANG=/L1031 &rem German

rem set ILANG=/L1040 &rem Italian (Standard)

rem set ILANG=/L1034 &rem Spanish - Traditional Sort

rem set ILANG=/L1029 &rem Czech

rem set ILANG=/L1045 &rem Polish

rem set ILANG=/L1046 &rem Portuguese (Brazil)

rem set ILANG=/L1049 &rem Russian

```

rem set ILANG=/L1041 &rem Japanese
rem set ILANG=/L1042 &rem Korean
rem set ILANG=/L1052 &rem Chinese (Simplified/PRC)
rem set ILANG=/L1028 &rem Chinese (Traditional/Taiwan)

rem -----
rem Set the Install-to directory
rem -----
rem set OPTIONS=%OPTIONS% INSTALLTO="C:\Program Files\Siemens\JT2Go\"

rem -----
rem set foreign language localizations to be installed (optional)
rem -----
rem set OPTIONS=%OPTIONS% INSTALL_SPANISH=1
rem set OPTIONS=%OPTIONS% INSTALL_GERMAN=1
rem set OPTIONS=%OPTIONS% INSTALL_FRENCH=1
rem set OPTIONS=%OPTIONS% INSTALL_ITALIAN=1
rem set OPTIONS=%OPTIONS% INSTALL_CZECH=1
rem set OPTIONS=%OPTIONS% INSTALL_PORTUGUESE=1
rem set OPTIONS=%OPTIONS% INSTALL_POLISH=1
rem set OPTIONS=%OPTIONS% INSTALL_JAPANESE=1
rem set OPTIONS=%OPTIONS% INSTALL_KOREAN=1
rem set OPTIONS=%OPTIONS% INSTALL_SCHINESE=1
rem set OPTIONS=%OPTIONS% INSTALL_TCHINESE=1
rem set OPTIONS=%OPTIONS% INSTALL_RUSSIAN=1

rem -----
rem Install a Desktop Shortcut. 1=yes, 0=no. Default=1
rem -----
rem set OPTIONS=%OPTIONS% DT_SHORTCUT=0

rem -----
rem Disable internet connection for JT2Go session. 1=yes, 0=no. Default=0
rem -----
rem set OPTIONS=%OPTIONS% DISABLE_INTERNET=1

rem -----
rem Disable automatic updates. 1=yes, 0=no. Default=0
rem -----
rem set OPTIONS=%OPTIONS% DISABLE_UPDATES=1

rem -----
rem set initial behavior for the Teamcenter Visualization Product Excellence Program
rem Valid values are:
rem 0: UI enabled, checkbox off (Product Excellence Program disabled, end user can change thru UI)
rem 1: UI disabled, checkbox off (Product Excellence Program disabled, end user cannot change)
rem 2: UI enabled, checkbox on (Product Excellence Program enabled, end user can change thru UI)
rem 3: UI disabled, checkbox on (Product Excellence Program enabled, end user cannot change)

```

```
rem -----
rem set OPTIONS=%OPTIONS% JT2GO_PEP_INIT=1

rem -----
rem Location of configuration file (optional)
rem Either use a UNC path to the version specific CONFIG_JT2Go file, or copy it locally.
rem -----
rem set OPTIONS=%OPTIONS% CONFIG="C:\temp\myConfig"

rem -----
rem Enable installer-time import of default registry settings. 1=yes, 0=no. Default=0
rem If not installed at install time, launching JT2Go for the first
rem time will import them anyway using regedit.
rem -----
rem set OPTIONS=%OPTIONS% IMPORTDEFAULTREG=1

rem launch the installer
%EXEFILE% %ILANG% %SILENTOPT1% /v"%SILENTOPT2% %OPTIONS%"

endlocal
```