

```
@echo off
rem -----
rem
rem This script provides a template for customizing and launching the
rem JT2Go 11.5 installer. Controlling the installer in this manner will:
rem
rem   * allow for preselection of features to be installed
rem   * prefill required fields (e.g. licensing options)
rem   * ease deployment to a large number of users.
rem
rem To use this script, simply uncomment and fill in the proper options
rem below, and choose the proper options for the install, or feel free
rem to otherwise modify it to fit your situation.
rem
rem For some Windows Installer options, there are more possible values than
rem are listed here. For the complete Windows Installer command line reference, see
rem http://msdn.microsoft.com/library/default.asp?url=/library/en-us/msi/setup/command_line_options.asp
rem
rem -----
setlocal

set EXEFILE=JT2GoSetup.exe
set OPTIONS=

rem -----
rem Silent mode. OPT1 is for the .exe wrapper, OPT2 is standard Windows
rem Installer silent mode option. Both must be set.
rem -----
rem set SILENTOPT1=/S &set SILENTOPT2=/qb

rem -----
rem Installer logging
rem -----
rem set OPTIONS=%OPTIONS% -I*v C:\temp\JT2GoIns.log

rem -----
rem set the language in which to run the installer
rem -----
set ILANG=/L1033 &rem English
rem set ILANG=/L1036 &rem French (Standard)
rem set ILANG=/L1031 &rem German
rem set ILANG=/L1040 &rem Italian (Standard)
rem set ILANG=/L1034 &rem Spanish - Traditional Sort
rem set ILANG=/L1029 &rem Czech
rem set ILANG=/L1045 &rem Polish
rem set ILANG=/L1046 &rem Portuguese (Brazil)
```

Unrestricted

```
rem set ILANG=/L1049 &rem Russian
rem set ILANG=/L1041 &rem Japanese
rem set ILANG=/L1042 &rem Korean
rem set ILANG=/L1052 &rem Chinese (Simplified/PRC)
rem set ILANG=/L1028 &rem Chinese (Traditional/Taiwan)

rem -----
rem Set the Install-to directory
rem -----
rem set OPTIONS=%OPTIONS% INSTALLTO=\"C:\Program Files\Siemens\JT2Go\"

rem -----
rem set foreign language localizations to be installed (optional)
rem -----
rem set OPTIONS=%OPTIONS% INSTALL_SPANISH=1
rem set OPTIONS=%OPTIONS% INSTALL_GERMAN=1
rem set OPTIONS=%OPTIONS% INSTALL_FRENCH=1
rem set OPTIONS=%OPTIONS% INSTALL_ITALIAN=1
rem set OPTIONS=%OPTIONS% INSTALL_CZECH=1
rem set OPTIONS=%OPTIONS% INSTALL_PORTUGUESE=1
rem set OPTIONS=%OPTIONS% INSTALL_POLISH=1
rem set OPTIONS=%OPTIONS% INSTALL_JAPANESE=1
rem set OPTIONS=%OPTIONS% INSTALL_KOREAN=1
rem set OPTIONS=%OPTIONS% INSTALL_SCHINESE=1
rem set OPTIONS=%OPTIONS% INSTALL_TCHINESE=1
rem set OPTIONS=%OPTIONS% INSTALL_RUSSIAN=1

rem -----
rem Install a Desktop Shortcut. 1=yes, 0=no. Default=1
rem -----
rem set OPTIONS=%OPTIONS% DT_SHORTCUT=0

rem -----
rem Disable internet connection for JT2Go session. 1=yes, 0=no. Default=0
rem -----
rem set OPTIONS=%OPTIONS% DISABLE_INTERNET=1

rem -----
rem Disable automatic updates. 1=yes, 0=no. Default=0
rem -----
rem set OPTIONS=%OPTIONS% DISABLE_UPDATES=1

rem -----
rem Location of configuration file (optional)
rem Either use a UNC path to the version specific CONFIG_JT2Go file, or copy it locally.
rem -----
rem set OPTIONS=%OPTIONS% CONFIG="C:\temp\myConfig"
```

Unrestricted

```
rem -----
rem Enable installer-time import of default registry settings. 1=yes, 0=no. Default=0
rem If not installed at install time, launching JT2Go for the first
rem time will import them anyway using regedit.
rem -----
rem set OPTIONS=%OPTIONS% IMPORTDEFAULTREG=1

rem launch the installer
%EXEFILE% %ILANG% %SILENTOPT1% /v"%SILENTOPT2% %OPTIONS%"

endlocal
```